PRODUCT SHEET POUCHES

3L Pouch-Up® DG

A'/amkF / VTm-1 (272*240) / Double Gusset

- 3L manufactured flexible pouch (272x240mm) without unit outer box.
- Quadruplex aluminium film of 156µm, giving an excellent barrier to oxygen and UV while guaranteeing a perfect package stability.
- Tap outside concept: Standard Vitop® with its tamper evident features.
- Integrated handle "one hole + ellipse" + specific cutting.
- Double gusset, top and bottom (neutral) for a free-standing packaging allowing easy storage and dispensing *.
- * Specific colours possible under conditions




QUADRUPLEX PET/ALU/OPA/PE

Standard applications (filling at ambient T° /adapted to long transportation) and hot filling.

Opacity.

Oxygen permeability : < 0.1 cc /m 2 /24h at 23°C, 75%HR and 100% O $_2$ (new film).

 $Printing: Heliography\,up\,to\,8\,colours.$



Closure

amkF/VTm

Standard Vitop® tap: PP, HDPE, elastomer, aluminium foil Spout: LDPE.



Filling of Pouches

Nitrogen injection is recommended in order to have a sufficient cone to:

- Have a better aspect of pouches in shops (pouches look blown).
- Have a better maintaining in boxes and enhance the resistance during transport.
- Reduce the quantity of O₂ in pouches and have a better product shelf life.
- Make the filling cleaner (no splashes during filling).

For this specification, the optimal cone should be around: **160ml+/-20ml.**

Filling Machines

Use of Smurfit Kappa machine is recommended:

- ½ automatic VITOP machine with cradle.
- Fully automatic SK BIB 700E machine.





APPLICATIONS / FILLING *:

| ☑ Clean | ☑ Hot filling | ΠAsentic |
|---------|---------------|----------|
| | | |

* Please look at the suitable GMP guides available

PRODUCT TYPE:

| ☑ Wine (recommendation: CO ₂ <500 mg/l) | □ Non food | |
|--|----------------------------|--|
| ☐ Fruit puree and concentrate | □ Water | |
| ☐ Industrial food (sauces,) | ☑ Dairy product (fresh) | |
| ☑ Post mix/Syrup | ☑ Oil | |
| ☑ Juices | □Eggs | |
| | | |

 $\ensuremath{\square}$ Alcoholic Beverage (optimal storage and transport conditions 20°C):

to perform on the final product, see RD-EN-067)

Weight of the pouch

48 grs

Delivery

260 Pouch-Up® / box – 14 boxes /Pallet => 3640 Pouch-Up® / pallet

AVAILABLE DOCUMENTATION

- ☑ Technical specs
- ☑ Food contact cert.
- ☑ Closure sheet
- ☑ GMP Guidelines
- ☑ Retroplanning

Transport recommandations:

| Positioning into the surrounding box | Local transport < 1000km | Short Export < 2000km (no maritime) | International Export > 2000km & maritime transport |
|--------------------------------------|-----------------------------|--|---|
| Vertical | YES | YES | YES |
| Horizontal | YES | YES | YES |

HORIZONTAL PACKING

Internal dimensions => 292 x 258 x

RECOMMENDATIONS FOR INTERNAL DIMENSIONS:

VERTICAL PACKING

Internal dimensions => 292 x 258 x 230mm


- To simplify the fitting into the box, pouches can be fitted upside down
- In this case, boxes must be reversed for paletisation and transport (tap down)





Surrounding boxes

- Composition of the board, external dimensions of boxes and palletisation have to be checked and validated with the corrugated box supplier.
- For better strength resistance of the board, divider can be used in the boxes (especially for horizontal packing).
- Preferably use boxes with jointed flaps in order to have a similar maintaining for each pouch in the box.




Palletisation of filled pouches

- The final palletisation must be in accordance with logistic constraints and requirements of the customer.
- Maximum height and weight of pallets must be defined by the customer.

EXAMPLES OF POSSIBLE PALLETISATION:

VERTICAL & HORIZONTAL PACKING

Pal 800 x 1200 => 48 Pouch-Up® / layer




| Nb layers | | Pal Height | Liters / Pal |
|-----------|-----|---------------|-----------------|
| 4 | 192 | 1,13m | 576 |
| 5 | 240 | 1,38m | 720 |
| 6 | 288 | 1,63m | 864 |

Composition of the board to define (4mm flutes used for simulation)

* HORIZONTAL PACKING FOR INTERNATIONAL

Pal 800 x 1200 => 48 Pouch-Up® / layer



| Nb layers | Nb / Pal | Pal Height | Liters / Pal |
|-----------|----------|---------------|-----------------|
| 4 | | 1,09m | 576 |
| 5 | 240 | 1,33m | 720 |
| 6 | 288 | 1,57m | 864 |

All configurations must be approved by transport trials or/and during the first order by the customer.

All these data are given in good faith. We recommend to all our customers to carry out their own tests to ensure that they are fully satisfied with the suitability of the filling process the product and the transport.